

[See all 13 Products in Family](#)

50X Oil Immersion Objective, CFI Plan Achromatic

See More by [Nikon](#)



Stock **#75-357** NEW **1 In Stock**

-

1

+

S\$1,708⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,708.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
MRL01502	
Compatible Tube Lens Focal Length (mm):	
Focal Length: 200mm	
Type:	
Microscope Objective	
Style:	
Infinity Corrected	
Manufacturer:	
Nikon	

Physical & Mechanical Properties	
0.44	Field of View (mm):
59.67	Length excluding Threads (mm):
27.5	Maximum Diameter (mm):
165	Weight (g):
Optical Properties	
0-0.17	Compatible Cover Glass Thickness (mm):
0.128	Horizontal Field of View, 1/2" Sensor:
0.176	Horizontal Field of View, 2/3" Sensor:
50X	Magnification:
0.90	Numerical Aperture NA:
0.35	Working Distance (mm):
22	Field Number (mm):
60.02	Parfocal Length (mm):
Oil	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M25 x0.75	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1X to 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1X up to 100X magnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.