

TECHSPEC<sup>®</sup> 5mm 1064nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #48-576 6 In Stock

-

1

+

S\$369<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$369.60 each                |
| Qty 6-25       | S\$299.60 each                |
| Qty 26-99      | S\$271.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                     |
|----------------------------------|---------------------|
| Linear Polarizer                 | Type:               |
| Physical & Mechanical Properties |                     |
| Protective as needed             | Bevel:              |
| 90.00                            | Clear Aperture (%): |

|                                  |                                     |
|----------------------------------|-------------------------------------|
| Cube                             | Construction:                       |
| 5.0 x 5.0 x 5.0 ±0.1             | Dimensions (mm):                    |
| Optical Properties               |                                     |
| ±3                               | Beam Deviation (arcmin):            |
| R <sub>abs</sub> <0.25% @ 1064nm | Coating Specification:              |
| 1064                             | Design Wavelength DWL (nm):         |
| 1000:1                           | Extinction Ratio:                   |
| >95                              | P-Polarization Transmission (%):    |
| >99.5                            | S-Polarization Reflection (%):      |
| N-BK7                            | Substrate: <input type="checkbox"/> |
| 40-20                            | Surface Quality:                    |
| 1.25                             | Power (fringes) @ 632.8nm:          |
| 0.25                             | Irregularity (fringes) @ 632.8nm:   |
| Regulatory Compliance            |                                     |
| Compliant                        | RoHS 2015:                          |
| Compliant                        | Reach 219:                          |
| View                             | Certificate of Conformance:         |


## Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision [right angle prisms](#) cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

## Technical Information