

TECHSPEC[®] 5mm Dia., 1mm Thick, Uncoated, Lithium Fluoride (LiF) Window



Lithium Fluoride (LiF) Windows

Stock **#19-724** **7 In Stock**

-

1

+

S\$190⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$190.40 each
Qty 11-25	S\$170.80 each
Qty 26-49	S\$162.40 each
Need More?	Request Quote

Product Downloads

General	
Protective Window	Type:
Physical & Mechanical Properties	
Protective as needed	Bevel:
90	Clear Aperture (%):

4.50	Clear Aperture CA (mm):
5.00 +0.00/-0.10	Diameter (mm):
1.00 ±0.10	Thickness (mm):
Fine Ground	Edges:
102.00	Knoop Hardness (kg/mm²):
<3	Parallelism (arcmin):
0.33	Poisson's Ratio:
64.97	Young's Modulus (GPa):

Optical Properties	
97.29	Abbe Number (v _d):
Random	Axis Orientation:
Uncoated	Coating:
1.392	Index of Refraction (n _d):
Lithium Fluoride (LiF)	Substrate:
λ/2 @ 632.8nm	Surface Flatness (P-V):
60-40	Surface Quality:
150 - 6000	Wavelength Range (nm):

Material Properties	
37	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):
2.64	Density (g/cm³):

Regulatory Compliance	
View	Certificate of Conformance:


Product Details

- High Transmission from 150nm - 6µm
- Excellent Vacuum UV (VUV) Transmission
- Low Index of Refraction

Lithium Fluoride (LiF) Windows provide high, flat transmission from 150nm to 6µm. Lithium fluoride has excellent transmission in the vacuum ultraviolet (VUV) wavelength range of 150 - 200nm. Lithium fluoride also has a low index of refraction, allowing these windows to be used without an anti-reflection (AR) coating. Lithium Fluoride (LiF) Windows are ideal for use as UV transmission windows in spectroscopy applications, as a diffracting element in X-ray spectrometry, or as infrared windows for thermal imaging applications.

Note: Lithium fluoride is sensitive to thermal shock and is attacked by atmospheric moisture at temperatures above 400°C.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

