


5mm Diameter High Contrast VIS-NIR Polarizer



Stock **#90-383** NEW **1 In Stock**

-

1

+

S\$425^{.65}

ADD TO CART

Volume Pricing	
Qty 1-10	S\$425.65 each
Qty 11+	S\$340.52 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General	
Linear Polarizer	Type:
Physical & Mechanical Properties	
Clear Aperture CA (mm):	

4.50	
5.00 +0.0/-0.2	Diameter (mm):
2.00 ±0.20	Thickness (mm):
Nanoparticle	Construction:
90	Clear Aperture (%):
Optical Properties	
Double-Side AR Coat	Coating:
>100,000:1 (700nm) >10,000:1 (600 to 850nm) >1,000:1 (600 to 1000nm)	Extinction Ratio:
Sodium Silicate Glass Doped with Glass Nanoparticles	Substrate: ☐
40-20	Surface Quality:
>78%	Transmission (%):
<λ/4 @ 633nm per 1cm	Transmitted Wavefront, P-V:
<1	Beam Deviation (arcmin):
<0.5 (to indicated edge)	Polarization Axis Mark (%):
600 - 1000	Wavelength Range (nm):
Continuous block Continuous pass Pulse peak power Equivalent pulse power density 10 W/cm² 25 W/cm² 12 MW/cm² 1 μJ/cm²	Damage Threshold, By Design: ☐
±20	Acceptance Angle (°):
Threading & Mounting	
Unmounted	Mount Thickness (mm):
Environmental & Durability Factors	
-20 to +120	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25μm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

TECHNICAL INFORMATION

