

5mm FL Wide Angle Low Distortion Lens



#68-670

Stock **#68-670** 20+ In Stock

-

1

+

S\$1,229⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,229.00 each
Need More?	Request Quote

Product Downloads

General	
Low Distortion Wide Angle Lenses	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Fixed	Iris Option:
38.20	Length (mm):

42.0	Maximum Diameter (mm):
42	Outer Diameter (mm):
75.00	Weight (g):
Optical Properties	
200.00	Field of View @ Min Working Distance (mm):
82.4°	Horizontal Field of View, 2/3" Sensor:
65.2°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
5.00	Focal Length FL (mm):
150 - ∞	Working Distance (mm):
f/2.8	Aperture (f/#):
<0.5	Distortion (%):
<0.5	Maximum Distortion (%):
VIS	Lens Wavelength Range:
Sensor	
2/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):
Threading & Mounting	
M40.5 x0.50	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.