

5mm Diameter, Truncated B270 Half-Ball Lens



B270 Half-Ball Lenses

Stock **#21-903** **4 In Stock**

S\$56⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	S\$56.00 each
Qty 11-25	S\$47.25 each
Qty 26-49	S\$42.35 each
Need More?	Request Quote

Product Downloads

General

Half-Ball Lens **Type:**

Physical & Mechanical Properties

5.00 ±0.1 **Diameter (mm):**

2.20 ±0.15 **Center Thickness CT (mm):**

2.50

Radius R (mm):

Optical Properties

B270

Substrate:

Uncoated

Coating:

360 - 2700

Wavelength Range (nm):

1.523

Index of Refraction (n_d):

Regulatory Compliance

Compliant

RoHS 2015:

Compliant

Reach 224:

[View](#)

Certificate of Conformance:

Product Details

- Available in Truncated and Extended Geometries
- High Transmission in the Visible and NIR
- Ideal for Cost Sensitive Applications

B270 Half-Ball Lenses feature a molded spherical surface and polished plano surface, facilitating easier mounting compared to ball lenses. The B270 substrates have high transmission from the visible to the near infrared (NIR) and have a similar refractive index to N-BK7, making these lenses an ideal alternative for cost sensitive applications. Each diameter of lens is available in two form factors, truncated (hypo-hemisphere) and extended (hyper-hemisphere), providing options to best meet system mechanical requirements. B270 Half-Ball Lenses are used in high power LED, fiber coupling, endoscopy, microscopy, and laser measurement applications.