

[See all 7 Products in Family](#)

3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range)



3W Deuterium/3W Tungsten Lamp Source (UV-VIS-NIR Range), #57-055

Stock **#57-055** [CONTACT US](#)

- 1 +

SS\$4,193⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	SS\$4,193.00 each
Need More?	Request Quote

Product Downloads

General

Note:
External power supply and AC cord included. Fiber patchcord listed under Accessories tab sold separately.

Lamp Lifetime (hours):
≥1000 / ≥2000

Physical & Mechanical Properties

Dimensions (mm):
171 x 76 x 64

Optical Properties	
200 - 1100	Wavelength Range (nm):
Electrical	
3W Deuterium, 3W Tungsten, 6W Both	Output Power (W):
Hardware & Interface Connectivity	
SMA-905	Connector:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.