

TECHSPEC® 6" Diameter x 24" FL Protected Aluminum, Parabolic Mirror



Stock #32-069-522 3-5 DAYS

- 1 + **S\$987.45**

ADD TO CART

Qty 1-4
S\$987.45
Qty 5+
S\$839.55
Volume Pricing
Request Quote

Get Product Downloads

Substrate: 

Focal Length Tolerance (%):
±1

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 6.0 +0.06/-0
Diameter (mm): 152.40 +1.5/-0
Effective Focal Length EFL (inches): 24.0
Effective Focal Length EFL (mm): 609.60
Radius of Curvature (mm): 1,219.20
Aperture (f/#): f/4
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 138
Edge Thickness ET (inches): 1.00
Edge Thickness ET (mm): 25.40
Type: Parabolic Mirror
Wavelength Range (μm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant