


TECHSPEC[®] 600 - 1000nm, 50.8mm Dia. Ultrafast-Enhanced Silver Laser Mirror



Stock #13-061 14 In Stock

-

1

+

S\$333^{.20}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$333.20 each
Qty 5-9	S\$295.40 each
Qty 10+	S\$263.20 each
Need More?	Request Quote

Product Downloads

General

Flat MirrorType:

Physical & Mechanical Properties

<3Parallelism (arcmin):

90Clear Aperture (%):

Commercial Polish	Back Surface:
50.80 +0.00/-0.10	Diameter (mm):
9.53 ±0.20	Thickness (mm):
Ground, protective bevel as needed	Edges:

Optical Properties

10-5	Surface Quality:
R _{avg} >99% @ 600 - 1000nm, 0° R _s >99% @ 540 - 1000nm, 45° R _p >98.5% @ ~730 - 870nm, 45°	Coating Specification:
0 ±20fs ² @ 600 - 1050nm	GDD Specification:
600 - 1000	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
Ultrafast-Enhanced Silver	Coating Type:
Ultrafast-Enhanced Silver (600-1000nm)	Coating:
Fused Silica (Corning 7980)	Substrate: ☐
0.3 J/cm ² @ 800nm, 48fs, 1 pulse (typical) 0.16 J/cm ² @ 800nm, 48fs, 100Hz, 1000 pulses (typical)	Damage Threshold, Reference: ☐

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 223:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Reflectivity >99% at 600 – 1000nm or 800 – 1150nm
- Low Group Delay Dispersion as Low as 0 ±20fs²
- Ideal for Ti:sapphire and Yb:doped Lasers
- Standard Imperial Sizes Available
- **TECHSPEC® Ultrafast-Enhanced Silver Concave Laser Mirrors** Available

TECHSPEC® Ultrafast-Enhanced Silver Laser Mirrors feature silver coatings that are enhanced with a dielectric coating to provide increased reflectivity at 600 – 1000nm or 800 – 1150nm. These mirrors have an intrinsically low group delay dispersion (GDD) within their broad wavelength range, making them ideal for the fundamental wavelength of Ti:sapphire lasers. TECHSPEC Ultrafast-Enhanced Silver Laser Mirrors are available with standard imperial sizes for easy integration into optical systems. For dielectric coated laser mirrors with low GDD at other ultrafast laser wavelengths, see our [Low GDD Ultrafast Mirrors](#).

Technical Information



600-1000nm Ultrafast-Enhanced Silver

Compatible Mounts