

[See all 12 Products in Family](#)

60mm Center of Rotation, Motorized Goniometer Stage, Integrated Controller

See More by [Zaber™](#)



Stock **#26-076** 1 In Stock

-

1

+

S\$3,829⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$3,829.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
	Type:
Metric	
	Encoder:
No	
	Manual Control:
Yes	
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232	

connectivity. A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control simultaneously.

2-Phase Stepper	Type of Motor:
Physical & Mechanical Properties	
Goniometer	Type of Movement:
Crossed Roller Bearing	Guide System:
40 x 40	Stage Size (mm):
±7	Travel (°):
0.06, Unidirectional	Accuracy (°):
< 0.01	Backlash (°):
20.8	Height (mm):
3	Load Capacity (kg):
30 (Centered Load)	Load Capacity (N):
60	Radius R (mm):
< 0.005	Repeatability (°):
1.975	Resolution (μrad):
Max: 30	Speed (°/s):
0.271	Weight (kg):

Electrical	
350	Current (mA):

Hardware & Interface Connectivity	
Precision Worm Gear	Type of Drive:
Power Supply Required and Sold Separately: USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294	Power Supply:
USB with #15-295 RS-232 with #15-297	Computer Interface:

Environmental & Durability Factors	
0 to +50	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- 40mm and 60mm Center of Rotation Options
- Vacuum-Compatible Options
- Small Footprint with a Low Profile for Compact Systems
- 30N (~3kg) Centered Load Capacity
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ Motorized Goniometers provide electronically controlled, precise angular adjustment of an object about a fixed point located above the center of the mounting surface. Featuring a built-in controller, these goniometers can be controlled manually with an indexed control knob or computer controlled via RS-232 communication or via USB with the included software. Encoder version are available for all travel options, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ Motorized Goniometers are ideal for providing tip and tilt adjustment for optical components in laser alignment and beam steering applications. These goniometers feature an interlocking alignment system to ensure a common center of rotation when the 40mm and 60mm options are stacked, and can be daisy-chained with additional stages using only one power supply for ease of system integration.

Note: A24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.

