

60mm Motorized Rotary Stage, Integrated Controller, Rotary Encoder

See More by [Zaber™](#)



60mm Motorized Rotary Stage, #15-291

Stock **#25-043** **2 In Stock**

-

1

+

S\$4,214^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$4,214.00 each
Need More?	Request Quote

Product Downloads

General	
Universal (Metric & English)	Type:
Yes	Encoder:

Zaber X-RSW60A-E03	Model Number:
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to	

control simultaneously.	
Rotary	Encoder Type: Quadrature Encoder
Physical & Mechanical Properties	
Rotary	Type of Movement:
82.6 x 144.8	Stage Size (mm):
360	Travel (°):
0.08, Unidirectional	Accuracy (°):
<0.04	Backlash (°):
23mm Clear Aperture to hold a 25mm (1") Dia. Optic (up to 3mm Thick)	Center Hole:
20	Load Capacity (kg):
200	Load Capacity (N):
<0.02	Repeatability (°):
4.1	Resolution (μrad):
0.0001 to 115	Speed (°/s):
0.66	Weight (kg):
60	Table Diameter (mm):
200 CPR	Encoder Resolution:
225	Max. Continuous Torque (N⋅cm):

Electrical	
950	Maximum Operating Current (mA):

Hardware & Interface Connectivity	
Stepping Motor	Type of Drive:
Not included, see the Accessories tab for recommended 24 to 48V Power Supply & Tech Info tab for connector information.	Power Supply:
USB with #15-295 RS-232 with #15-297	Computer Interface:

Environmental & Durability Factors	
0 - 50	Operating Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- High Resolution with 360° Continuous Rotation
- Integrated Motor and Controller
- Vacuum-Compatible Options
- Controlled Manually or via RS-232 Serial Interface
- Power Supply and Data Cable Sold as Separate Accessories
- Available with Integrated, 200 Counts per Revolution (CPR) Motor Mounted Encoder

Zaber™ Motorized Rotary Stage Systems are designed to hold 1" or 25mm optical components on both the top and bottom plates, and provide precise, 360° rotation. The compact bearing design can handle up to 45 lb (20kg) loads while providing 4.1μrad resolution rotational movement. Encoder versions are available for all travel lengths, with 200 Counts per Revolution (CPR) rotary quadrature encoders integrated into the stepper motor. Zaber™ Motorized Rotary Stage Systems also includes a potentiometer located on the back of the stage to provide a convenient way to manually control position.

Note: A24-48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories. These stages utilize the same accessories as the [Zaber™ High Precision Motorized Stage System](#).

Technical Information

Device Overview / Connectors

Images are shown looking into the device.
Power

1

2

Pin	Description
1	24 - 48 V
2	GND (Note: power supplies ground this pin to AC Earth)

Note: To prevent damage to the device due to static buildup, the device should be properly grounded. The power supplies for X-Series devices are non-isolated and thus ground the device chassis to Earth via the negative terminal of the power supply. If for any reason you are using an isolated power supply, please ensure your device is grounded by connecting the negative terminal of the power connector to AC Earth.

