


TECHSPEC® 6.25mm Dia x -25mm Negative Doublet Lens FL MgF₂ Coated



Stock **#45-421** 3-5 DAYS

[Other Coating Options](#)

- 1 +

S\$97.15

ADD TO CART

Qty 1-5
S\$97.15
Qty 6+
S\$82.65
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.025

Effective Focal Length EFL (mm):
-25.00

Focal Length Tolerance (%):
±1

Back Focal Length BFL (mm): -26.53
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 5.625
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Center Thickness CT 1 (mm): 1.00 ±0.05
Center Thickness CT 2 (mm): 2.00 ±0.05
Radius R₁ (mm): -17.57
Radius R₂ (mm): 11.48
Radius R₃ (mm): 109.44
Edge Thickness ET (mm): 3.27
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 4.00
Numerical Aperture NA: 0.13
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Negative Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View