

[See all 6 Products in Family](#)

60X Water Immersion Objective, Nikon CFI60 Apo NIR

See More by [Nikon](#)



Stock #75-370 NEW 1 In Stock

-

1

+

\$S\$7,504^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	\$S\$7,504.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	MRD07620
Compatible Tube Lens Focal Length (mm):	Focal Length: 200mm
Type:	Microscope Objective
Style:	Infinity Corrected
Manufacturer:	Nikon

Physical & Mechanical Properties	
0.367	Field of View (mm):
58.50	Length excluding Threads (mm):
28	Maximum Diameter (mm):
125	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
0.107	Horizontal Field of View, 1/2" Sensor:
0.147	Horizontal Field of View, 2/3" Sensor:
60X	Magnification:
1	Numerical Aperture NA:
2.8	Working Distance (mm):
22	Field Number (mm):
60.5	Parfocal Length (mm):
Water	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M25 x0.75	Mounting Threads:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Water Dipping Design for Live Imaging
- Optimized for Infrared (IR) and Multiphoton Microscopy
- High NA for Superior Resolution

Nikon CFI60 Water Dipping Objectives design allows direct immersion into aqueous samples, reducing optical aberrations and enabling high-resolution, live imaging of thick specimens. These objectives are designed with high numerical apertures and long working distances and are available in a variety of magnifications. Featuring M25 x0.75 mounting threads, these objectives can be easily integrated into existing microscopy systems. Nikon CFI60 Water Dipping Objectives enable high-resolution, low-aberration imaging deep within living tissues by efficiently transmitting infrared light and correcting optical distortions specific to multiphoton and IR microscopy.