

62 x 147mm FL, Grade 1, Double-Convex Lens



Stock #31-795 CLEARANCE 20+ In Stock

-

1

+

\$7^{.35}

ADD TO CART

Volume Pricing	
Qty 1+	\$7.35 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

62.00	Diameter (mm):
-------	----------------

Optical Properties

147.00	Effective Focal Length EFL (mm):
--------	----------------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-convex (DCX) lenses have two outward curved surfaces, a positive focal length and are useful for 1:1 imaging and in multi-element systems.

50mm and Larger Experimental Quality Double-Convex (DCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

