

## 635nm 25.4mm META® holoOPTIX® STRATA Notch Filter



25.4mm META® holoOPTIX® STRATA Notch Filter

Stock #23-029 CLEARANCE 7 In Stock

⊖ 1 ⊕ \$510<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	<b>\$510.93</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Notch Filter Type:

### Physical & Mechanical Properties

25.40 ±0.2 Diameter (mm):

20 Clear Aperture CA (mm):

4.50 ±0.1 Thickness (mm):

Construction:  
Mounted in Black Anodized Ring

Clear Aperture (%):  
80

## Optical Properties

Optical Density OD (Average):  
>4.0

Center Wavelength CWL (nm):  
635.00

Surface Quality:  
60-40

Transmission (%):  
94% (400-600nm)  
96% (675-750)

Transmitted Wavefront, RMS:  
<1λ

Spectral Bandwidth @ OD1:  
16 (Typical)

## Threading & Mounting

Mount Thickness (mm):  
4.5

## Regulatory Compliance


Certificate of Conformance:  
[View](#)

## Product Details

- >OD 4.0 (Typical)
- Broad Transmission Range
- Unique Large Flexible Design
- META® refers to the registered trademark of Meta Materials Inc.

META® holoOPTIX® Notch Filters are ideal for laser analysis applications requiring specific wavelength rejection and high transmission of all other wavelengths. Available in either a standard 25.4mm rigid mounted configuration (STRATA) or in a unique 375mm x 70mm flexible configuration (FLEX), these filters can be used in fluorescence or Raman spectrometers to eliminate unwanted noise from the pump laser source to obtain the optimum signal-to-noise ratio. The flexible design can be easily be cut for system prototyping and integration. META® holoOPTIX® Notch Filters center wavelengths can be tuned by adjusting the angle of incidence while maintaining consistent notch center wavelengths for both p- and s- polarizations, even at high angles of incidence.

## Technical Information



## Compatible Mounts