

## 6.5mm Travel, 0.002mm Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#33-738** 1 In Stock

-

1

+

S\$246<sup>40</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | S\$246.40 each                |
| Qty 10-24      | S\$221.76 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

|          |               |
|----------|---------------|
| Metric   | Type:         |
| Mitutoyo | Manufacturer: |

Physical & Mechanical Properties

|     |                  |
|-----|------------------|
| 6.5 | Travel (mm):     |
|     | Graduation (mm): |

|                 |                           |
|-----------------|---------------------------|
| 0.002           |                           |
| 9.5             | Stem Diameter (mm):       |
| Plain/Spherical | Stem/Spindle:             |
| 9.5             | Stem Length (mm):         |
| 5               | Spindle Diameter (mm):    |
| 14              | Min. Spindle Length (mm): |
| 13              | Max. Diameter (mm):       |
| 55              | Overall Length (mm):      |

Hardware & Interface Connectivity

|                   |                |
|-------------------|----------------|
|                   | Type of Drive: |
| Metric Micrometer |                |

Regulatory Compliance

|                                  |                             |
|----------------------------------|-----------------------------|
|                                  | RoHS 2015:                  |
| <a href="#">Exempt</a>           |                             |
|                                  | Certificate of Conformance: |
| <a href="#">View</a>             |                             |
|                                  | REACH 241:                  |
| <a href="#">Contains SVHC(s)</a> |                             |

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
  - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

## Technical Information

