See all 215 Products in Family

TECHSPEC® 6mm Dia., 0.40 Numerical Aperture, Uncoated, Precision Aspheric Lens

TECHSPEC® Precision Aspheric Lenses

Stock **#29-960** **15 In Stock**

Other Coating Options

- 1 + S$586.60

ADD TO CART

Volume Pricing	
Qty 1-5	**S$586.60** each
Qty 6-10	**S$527.80** each
Qty 11-25	**S$481.60** each
Need More?	Request Quote

Product Downloads

General

Type:

Aspheric Lens

Physical & Mechanical Properties

Diameter (mm):

6.00 +0.00/-0.025

Centering (arcmin):

<3

Clear Aperture CA (mm):

5.60

Edge Thickness ET (mm):

2.24

Center Thickness CT (mm):

3.00 ±0.10

Bevel:

Protective as needed

Shape of Back Surface:

Plano

Optical Properties

Effective Focal Length EFL (mm):

7.50 @ 587.6nm

Numerical Aperture NA:

0.40

Back Focal Length BFL (mm):

5.84

Substrate:

N-SF6

Aspheric Design Wavelength (nm):

587.6

Asphere Figure Error, RMS @ 632.8nm:

0.4λ

Coating:

Uncoated

Surface Quality:

40-20

f/#:

1.30

Wavelength Range (nm):

390 - 2500

Conjugate Distance:

Infinite

Power (diopters):

133.33

Regulatory Compliance

Certificate of Conformance:

View

Product Details

- Improved Versions of Our Aspheric Lenses
- Precision Grade Aspheric Surfaces
- High Numerical Apertures to Maximize Throughput

TECHSPEC® Precision Aspheric Lenses are CNC polished aspheric lenses that feature a 0.4λ RMS aspheric figure error. The precision aspheric figure error makes these lenses ideal for applications that require spherical aberration correction, including imaging and laser focusing applications. These aspheric lenses can also be used to replace multiple spherical elements in optical assemblies to reduce weight and cost. TECHSPEC Precision Aspheric Lenses are available with diameters from 6 to 50mm and high numerical apertures to maximize light throughput.

;