

37mm Max. Aperture, Mounted Stainless Steel Iris Diaphragm



Stock **#62-659** [CONTACT US](#)

-

1

+

S\$219^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$219.80 each
Qty 5-9	S\$193.62 each
Qty 10-25	S\$178.92 each
Need More?	Request Quote

Product Downloads

General

Type:	
Mounted	

Physical & Mechanical Properties

Maximum Aperture (mm):	
37.0	
Outer Diameter (mm):	
66.0	

Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators	Construction:
	Lever Diameter (mm):
	3.00
12.50	Lever Length (mm):
	16.00
16.00	Number of Leaves:
	9.50
9.50	Thickness (mm):
	1.6

Optical Properties

Minimum Aperture (mm):	1.6
------------------------	-----

Regulatory Compliance

RoHS 2015:	Exempt
Certificate of Conformance:	View
Reach 235:	Contains SVHC(s)

Product Details

- Stainless Steel and Brass Construction for Stability
- Mounted Version Features both an English and Metric Tapped Hole for Easy Post Mounting
- Ideal for Flow Control Applications

Stainless Steel Series Iris Diaphragms are designed with stainless steel lever pins and leaves within a blackened brass housing; these units will not rust or corrode under unstable environmental conditions. These diaphragms offer exceptionally smooth operation over the approximately 90° lever travel, from maximum to minimum aperture. Mounted versions of these diaphragms feature both a Metric and English tapped hole for easy post mounting. These diaphragms are offered with maximum apertures of 8 – 75mm, and with outer diameters ranging from 14.8 to 100mm. Stainless Steel Series Iris Diaphragms are ideal for dynamic control of beam width and light throughput in optical systems where environmental factors are a concern.

For specific OEM application assistance, please contact our [Applications Engineering Department](#).

Note: [Iris Diaphragm Mounts](#) sold separately.

Technical Information

Outside Diameter A	Maximum Aperture B	Minimum Aperture C	Thickness D	Stock No.	
				Unmounted	Mounted
14.8	8.0	0.8	4.5	#62-650	—
19.8	12.0	0.9	5.0	#53-910	#62-657
24.0	15.0	0.9	5.0	#64-501	—
28.0	18.0	0.9	5.0	#62-651	—
30.0	20.0	0.9	5.5	#64-502	—
33.0	22.0	0.9	5.5	#64-503	—
37.0	25.0	0.9	5.5	#53-911	#62-658
40.0	28.0	1.3	5.5	#64-504	—
50.0	36.0	1.6	6.0	#64-505	—
53.0	37.0	1.6	6.0	#53-912	#62-659
70.0	50.0	2.8	7.5	#53-913	#62-660
100.0	75.0	5.5	9.0	#62-652	—

