

TECHSPEC[®] 70R/30T NIR, C-Mounted Plate Beamsplitter



Stock **#49-689** **1 In Stock**

-

1

+

S\$458^{.50}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$458.50 each
Qty 5-9	S\$401.75 each
Qty 10+	S\$376.36 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Standard Beamsplitter

Beamsplitter Included:

[Standard 70R/30T NIR Plate Beamsplitter, 1 λ](#)

Physical & Mechanical Properties	
Plate	Construction:
+0.0/-0.25	Dimensional Tolerance (mm):
38.0	Extension Length (mm):
Black Anodized Aluminum	Housing:
38 x 38 x 50	Housing Dimension:
Optical Properties	
Surface 2: Multi-Layer Anti-Reflection for Near-Infrared Region	Coating Specification:
70/30	Reflection/Transmission Ratio (R/T):
±5	Reflection/Transmission Tolerance (%):
N-BK7	Substrate: ☐
1λ	Surface Flatness (P-V):
60-40	Surface Quality:
700 - 1100	Wavelength Range (nm):
Threading & Mounting	
C-Mount Enclosure	Mount:
C-Mount (1" x 32 TPI)	Thread Type:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Pre-Mounted 90 Degree Interface
 - Four C-Threaded Mounting Holes
 - Several Beamsplitting Options Available
 - Additional C-Mounted [Beamsplitters](#), [Filters](#), and [Mirrors](#) Available
- TECHSPEC® C-Mounted Plate Beamsplitters are designed to simplify system integration. These mounted beamsplitters include a TECHSPEC® Plate Beamsplitter pre-mounted in an Aluminum cube designed to interface with C-Mount (1" x 32 TPI) systems. Each cube is configured with four C-threaded holes, one on each face, and a ¼–20 tapped hole on the base for post mounting. TECHSPEC® C-Mounted Plate Beamsplitters are available in 30R/70T, 50R/50T, and 70R/30R options for either the visible or near infrared spectrum.
- The C-Mounted Visible Plate Beamsplitters are designed for the 400 - 700nm wavelength range and the C-Mounted NIR Plate Beamsplitters are designed for the 700 - 1100nm wavelength range.
- Note:** These products cannot be disassembled. For mounting an alternative beamsplitter in a C-Mount Cube, use either [#56-264](#) or [#56-265](#).

TECHNICAL INFORMATION

