

TECHSPEC[®] 75mm C Series Fixed Focal Length Lens



Stock #33-310 20+ In Stock

-

1

+

S\$375⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$375.00 each
Need More?	Request Quote

Product Downloads

General	
C Series	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:

98.76	Length (mm):
48	Maximum Diameter (mm):
48	Outer Diameter (mm):

7.24	Maximum Rear Protrusion (mm):
------	-------------------------------

Optical Properties

5.76°	Horizontal Field of View @ Max Sensor Format:
-------	---

	Field of View at Max Sensor Format: Horizontal: 5.76° Vertical: 4.32° Diagonal: 7.19°
--	--

5.76°	Horizontal Field of View, 2/3" Sensor:
-------	--

4.71°	Horizontal Field of View, 1/1.8" Sensor:
-------	--

4.19°	Horizontal Field of View, 1/2" Sensor:
-------	--

3.77°	Horizontal Field of View, 1/2.5" Sensor:
-------	--

3.14°	Horizontal Field of View, 1/3" Sensor:
-------	--

11.00	Maximum Image Circle (mm):
-------	----------------------------

0.05111	Numerical Aperture NA, Object Side:
---------	-------------------------------------

7 (6)	Number of Elements (Groups):
-------	------------------------------

75.00	Focal Length FL (mm):
-------	-----------------------

500 - ∞	Working Distance (mm):
---------	------------------------

f/2.0 - f/16.0	Aperture (f/#):
----------------	-----------------

425 - 675nm BBAR	Coating:
------------------	----------

425 - 675nm BBAR	Coating Specification:
------------------	------------------------

63.265	Entrance Pupil Position (mm):
--------	-------------------------------

-15.01	Object Space Principal Plane (mm):
--------	------------------------------------

-64.79	Image Space Principal Plane (mm):
--------	-----------------------------------

0.068	Maximum Distortion (%):
-------	-------------------------

-31.983	Exit Pupil Position (mm):
---------	---------------------------

VIS	Lens Wavelength Range:
-----	------------------------

Sensor

2/3"	Maximum Sensor Format:
------	------------------------

2.74	Pixel Size (µm):
------	------------------

Threading & Mounting

M43 x0.75 (Female)	Filter Thread:
--------------------	----------------

C-Mount	Mount:
---------	--------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Compact (C), FA Lens for Machine Vision
- 3.5mm to 100mm Focal Length

TECHSPEC® C Series Fixed Focal Length Lenses are designed for use in machine vision applications with the working distance and resolution requirements of factory automation and inspection in mind. TECHSPEC® C Series Fixed Focal Length Lenses feature large maximum apertures, allowing these high performance lenses to be used in even the most restrictive lighting conditions. Each lens has a broadband anti-reflection coating, locking iris and focus adjustment with recessed set screws, and a ruggedized, robust housing for space-restrictive applications. C Series lenses are manufactured to high tolerances, which result in high levels of imaging performance with low lens-to-lens variation. Through combining optical performance, industrial features, and compact package sizes, our TECHSPEC® C Series Fixed Focal Length Lenses are ideal for use in factory automation and inspection.

Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- C Series: Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\)](#) or [SWIR](#) Coating
- [Ci Series](#): Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- [Cr Series](#): All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- [Cx Series](#): Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- [Liquid Lens Cx Series](#): Designed with an integrated liquid lens for quick autofocus.
- [Cw Series](#): Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.

Technical Information

