

[See all 25 Products in Family](#)

780nm Single Stage Free-Space Optical Isolator



780nm Single Stage Free-Space Optical Isolator, #35-973

Stock **#35-973** **1 In Stock**

1 **\$6,608⁰⁰**

ADD TO CART

Volume Pricing

Qty 1-4	\$6,608.00 each
Qty 5+	\$5,950.00 each
Need More?	Request Quote

Product Downloads

General

Single Stage Optical Isolator **Type:**

Faraday **Style:**

Physical & Mechanical Properties

4.7 **Clear Aperture CA (mm):**

Optical Properties

85	Minimum Transmission (%)
92 (typical)	Transmission (%)
780	Design Wavelength DWL (nm)
750 - 810	Wavelength Range (nm)
40 W, 4 kW/cm ² @ DWL	Damage Threshold, By Design: <input type="checkbox"/>
43	Typical Isolation at Design Wavelength (dB)
38	Minimum Isolation at Design Wavelength (dB)
40 W, 4 kW/cm ² @ DWL	Damage Threshold, CW:
Environmental & Durability Factors	
+15 to +40	Operating Temperature (°C)
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 67 dB Isolation for Ultimate Stability
- Up to 92% Transmission for Maximum Power
- 4.7mm Input Aperture

Free-Space Optical Isolators incorporate a Faraday Rotator and are specifically designed and manufactured to provide superior performance with high isolation, transmission, and power densities. Each option effectively reduces feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators enable state of the art protection for the most stable lasers in the world and are ideal for demanding laser applications.

