

795nm Mini Single Stage Free-Space Optical Isolator



Mini Free-Space Optical Isolators

Stock #72-629 **CLEARANCE** 1 In Stock

⊖ 1 ⊕ **\$3,325.00**

ADD TO CART

Volume Pricing

Qty 1+	\$3,325.00 each
Need More?	Request Quote

Product Downloads

General

Single Stage Optical Isolator **Type:**
Faraday **Style:**

Physical & Mechanical Properties

7.69 **Length (mm):**
1.5 **Clear Aperture CA (mm):**

7.90 **Diameter (mm):**

Optical Properties

Minimum Transmission (%):
>70

Design Wavelength DWL (nm):
795

Damage Threshold, By Design:
60 W/cm² @ DWL

Minimum Isolation at Design Wavelength (dB):
>30

Environmental & Durability Factors

Operating Temperature (°C):
+15 to +40

Regulatory Compliance

Certificate of Conformance:
[View](#)

Product Details

- Small, <1cm³, Form Factor
- Greater than 70% Minimum Transmission and >30dB Minimum Isolation
- Input Apertures as Low as 1.60mm

Mini Free-Space Optical Isolators are designed around a less than 1cm³ form factor with an incorporated Faraday Rotator while maintaining a superior performance with high isolation, transmission, and power densities. These isolators effectively reduce feedback in the external cavity of diode laser systems and blocks reflections from free-space fiber coupling. Designed to be resistant to environmental temperature changes these isolators are capable of integration into systems with where fluctuating temperatures are a concern. Mini Free-Space Optical Isolators increase power stabilization in optical systems and also eliminate feedback-induced damage to sensitive optical components. These isolators are ideal for quantum technology applications such as quantum communication, simulation, cryptography, sensors, computing, and networks.

