

830nm SureLock Narrow Linewidth MM Fiber Coupled Laser

See More by [Coherent®](#)



Coherent® Surelock™ Mini-Benchtop Laser Systems



Stock **#70-756** **1 In Stock**

-

1

+

S\$8,526⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$8,526.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Note:
Recommended Fiber Patchcord: [#23-706](#)

Laser Class - CDRH:

Physical & Mechanical Properties

150 x 150 x 50	Dimensions (mm):
1.00	Weight (kg):

Optical Properties

0.22	Numerical Aperture NA:
0.07	Spectral Line Width (nm):

830.00 ±0.5	Center Wavelength CWL (µm):
-------------	-----------------------------

Electrical

500	Output Power (mW):
1.00	Input Current (A):

Hardware & Interface Connectivity

FC/PC	Connector:
90 - 240 (AC)	Input Voltage (V):

Environmental & Durability Factors

+10 to +35	Operating Temperature (°C):
-10 to +60	Storage Temperature (°C):

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

PRODUCT DETAILS

- Narrow 0.07nm FWHMSpectral Linewidth
- Extreme Temperature Insensitivity
- Ultra-Compact, Easy-to-Use Turnkey Laser System

Coherent® Surelock™ Mini-Benchtop Laser Systems provide temperature stabilized, narrow 0.07nm FWHMspectral linewidth laser output with powers up to <500mW. Featuring integrated current and temperature control, these lasers provide better than 1% power stability, <1 minute warm-up time, and extreme temperature insensitivity for consistent performance over the locked region. A convenient LCD touchscreen display allows for easy setup, output power adjustment, and integration into new and existing lab and OEMsystems. Coherent® Surelock™ Mini-Benchtop Laser Systems are ideal for a range of precision applications including Raman Spectroscopy, Metrology, Bio-Instrumentation, Sensing, and Analytical Instrumentation. These lasers can be operated standalone or with a computer using the built in USB port which allows for a wide range of programming languages via serial commands.