

8.5mm Dia. x 7.4mm FL, MgF₂ Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#35-037** 3-5 DAYS

[Other Coating Options](#)



1



S\$61.63

ADD TO CART

Qty 1-10

S\$61.63

Qty 11+

S\$54.08

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
8.50 +/-0.3

Effective Focal Length EFL (mm):
7.40 @587.6nm

Numerical Aperture NA:
0.57

Back Focal Length BFL (mm): 4.80
Substrate: Liba2000+
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 6.80
Edge Thickness ET (mm): 1.8
Center Thickness CT (mm): 4.00 ±0.20
f/#: 0.87
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 8.5
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant