

852nm High Performance Laser Line Filter 12.5mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-272** [CONTACT US](#)

[Additional Bandwidths](#)

-

1

+

S\$517.65

ADD TO CART

Qty 1+

S\$517.65

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.50 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Bandwidth (nm):
3.2

OD 5 Blocking Wavelength Range (nm) :
652 - 843.5 & 860.5 - 1106.6

OD 6 Blocking Wavelength Range (nm):

783.8 - 839.2 & 864.8 - 937.2
Optical Density OD (Average): ≥6.0
Clear Aperture CA (mm): ≥10
Center Wavelength CWL (nm): 852.00
Design Wavelength DWL (nm): 852
Full Width-Half Max FWHM (nm): 3.20 - 6.0
Substrate: ☐ Low Fluorescence N-BK7 or equivalent
Minimum Transmission (%): >90
Coating: Hard Coated
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.10
Transmission (%): >90
Type: Bandpass Filter
Blocking Wavelength Range (nm): 652 - 843.5 & 860.5 - 1106.6
Construction: Mounted in Black Anodized Ring
Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3
Mount Thickness (mm): 3.5 ±0.1
Substrate Thickness (mm): 2.0 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View