

852nm High Performance Laser Line Filter 12.5mm Dia.



High Performance Laser Line Bandpass Filters

Stock **#12-272** [CONTACT US](#)

[Additional Bandwidths](#)

-

1

+

S\$558^{.60}

ADD TO CART

Volume Pricing	
Qty 1+	S\$558.60 each
Need More?	Request Quote

Product Downloads

General	
Bandpass Filter	Type:
Physical & Mechanical Properties	
12.50 +0.0/-0.1	Diameter (mm):
≥10	Clear Aperture CA (mm):
±0.10	Thickness Tolerance (mm):

Mounted in Black Anodized Ring	Construction:
Physical Durability: ML-C-48497A Paragraphs 4.5.3.1, 4.5.3.2, 4.5.3.3, 4.5.4.2, and 4.5.5.3	
Substrate Thickness (mm):	
2.0 ±0.1	

Optical Properties

0 ±2	Angle of Incidence (°):
3.2	Bandwidth (nm):
OD 5 Blocking Wavelength Range (nm) : 652 - 843.5 & 860.5 - 1106.6	
OD 6 Blocking Wavelength Range (nm): 783.8 - 839.2 & 864.8 - 937.2	
≥6.0	Optical Density OD (Average):
852.00	Center Wavelength CWL (nm):
852	Design Wavelength DWL (nm):
3.20 - 6.0	Full Width-Half Max FWHM (nm):
Substrate: ☐	
Fused Silica	
>90	Minimum Transmission (%):
Coating:	
Hard Coated	
Surface Quality:	
60-40	
Transmission (%):	
>90	
Blocking Wavelength Range (nm): 652 - 843.5 & 860.5 - 1106.6	

Threading & Mounting

Mount Thickness (mm):	
3.5 ±0.1	

Environmental & Durability Factors

Environmental Durability: ML-STD-810F Paragraphs 501.4, 502.4, and 507.4	
---	--

Regulatory Compliance

Compliant	RoHS 2015:
Compliant	Reach 209:
Certificate of Conformance:	
View	

Product Details

- Over 90% Transmission at Specified Laser Lines
- Hard Coated Design
- Designed for Laser Applications

Available for use with common gas and solid state lasers, High Performance Laser-Line Bandpass Filters are designed to offer maximum transmission of stimulated emission, while eliminating noisy spontaneous emission. These laser line filters are available at popular diode and Nd:YAG laser lines, including 532nm, 785nm, and 1064nm. High Performance Laser-Line Bandpass Filters are ideal for laser-based fluorescence instrumentation, Raman spectroscopy, or for analytical or medical laser systems. Due to their steep edges, High Performance Laser-Line Bandpass Filters are excellent complements to TECHSPEC® Notch Filters and [Laser Line Longpass Filters](#).

Note: These filters are optimized for high spectral performance rather than high Laser Induced Damage Thresholds (LIDT). A typical LIDT for these filters is 0.1 J/cm² @ 532nm, 10ns.

Technical Information



Compatible Mounts