

[See all 13 Products in Family](#)

86 x 28.8mm LED IR Bar Light 940nm

See More by [CCS](#)



86 x 28.8mm LED IR Bar Light 940nm

Stock **#21-846** 1 In Stock

-

1

+

S\$1,309⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,309.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
LDL-74X27IR2-940	Model Number:
LED Illuminator	Type of Illumination:
CCS	Manufacturer:
Bar Light	Geometry:

Constant	Illumination Mode:
Physical & Mechanical Properties	
W 86 mm x D 28.8 mm x H 18 mm	Dimensions (mm):
80	Weight (g):
74 x 27.2	Active Area (mm):
Optical Properties	
IR	Color:
940	Wavelength (nm):
Electrical	
6.9	Power Consumption (W):
Hardware & Interface Connectivity	
24	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #73-491 Europe: #73-491 Japan: #89-513 Korea: #33-773 China: #73-491	
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- 850 or 940nm Wavelength Options
- Compact Lightweight Housing
- Single and 4-Bar Configurations Available

CCS Infrared (IR) Bar Lights provide uniform infrared illumination along a localized area. Designed with a compact lightweight housing, these bar lights can be easily integrated into applications with a limited working area. CCS Infrared (IR) Bar Lights are ideal for a variety of testing and inspection applications in industrial and manufacturing environments such as foreign material detection, color reduction in monochromatic images, and character isolation for optical character recognition (OCR). These bar lights are available as a single bar light or as a 4-bar square configuration with both options featuring adjustable output angles. Compared to visible light, infrared light provides a lower scattering rate and a higher transmittance rate, allowing for fewer surface reflections and deeper penetration into materials for imaging.

Technical Information

