

8mm FL SWIR Series Fixed Focal Length Lens



Stock #83-815 **7 In Stock**

⊖ 1 ⊕ \$3,201.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	\$3,201.00 each
Need More?	Request Quote

Product Downloads

General

Series:
1" SWIR Series Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):
58.00

Maximum Diameter (mm):

57.0

Outer Diameter (mm):

57

Weight (g):

205

Optical Properties

Field of View @ Min Working Distance (mm):

165.00

Horizontal Field of View, 1" Sensor:

79.7°

Maximum Image Circle (mm):

16.00

Focal Length FL (mm):

8.00

Working Distance (mm):

100 - ∞

Aperture (f/#):

f/1.4 - f/16

Distortion (%):

<-2.0

Maximum Distortion (%):

-1.2

Lens Wavelength Range:

SWIR

Sensor

Maximum Sensor Format:

1"

Pixel Size (µm):

4.50

Threading & Mounting

Filter Thread:

M55.0 x 0.75

Mount:

C-Mount

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

REACH 241:

[Contains SVHC\(s\)](#)

Product Details

- 1", C-Mount Lens
- Spectral Range of 800 - 2000nm for InGaAs SWIR Sensors
- 8mm to 50mm Focal Lengths

Short Wave Fixed Focal Length Lenses are the best choice for use with SWIR cameras. The SWIR spectrum is an ideal choice for a variety of applications, including solar cell inspection, security, and biomedical imaging. When utilized in conjunction with a SWIR camera, these lenses will permit imaging through silicon, imaging outdoors without additional illumination, detecting bruising on fruit, and a host of additional infrared applications.

Technical Information

SWIR Fixed Focal Length Lenses



