

TECHSPEC<sup>®</sup> 9.0mm Diameter x 22.0mm FL, 785nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex(PCX) Lenses



Stock **#69-474** 11 In Stock

☐ [Other Coating Options](#)

-

1

+

S\$70<sup>70</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | S\$70.70 each                 |
| Qty 10-25      | S\$63.70 each                 |
| Qty 26-49      | S\$56.70 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):


|                           |                      |
|---------------------------|----------------------|
| 9.00 +0.0/-0.025          |                      |
| Centering (arcmin):       | <1                   |
| Center Thickness CT (mm): | 1.93 ±0.05           |
| Edge Thickness ET (mm):   | 1.00                 |
| Clear Aperture CA (mm):   | 8.1                  |
| Bevel:                    | Protective as needed |

|                                                       |                                   |
|-------------------------------------------------------|-----------------------------------|
| Optical Properties                                    |                                   |
| Effective Focal Length EFL (mm):                      | 22.00 @ 587.6nm                   |
| Back Focal Length BFL (mm):                           | 20.73                             |
| Coating:                                              | Laser V-Coat (785nm)              |
| Coating Specification:                                | R <sub>abs</sub> <0.25% @ 785nm   |
| Substrate: <input type="checkbox"/>                   | N-BK7                             |
| Surface Quality:                                      | 40-20                             |
| Power (P-V) @ 632.8nm:                                | 1.5λ                              |
| Irregularity (P-V) @ 632.8nm:                         | λ/4                               |
| Focal Length Tolerance (%):                           | ±1                                |
| Radius R <sub>1</sub> (mm):                           | 11.37                             |
| f#:                                                   | 2.44                              |
| Numerical Aperture NA:                                | 0.20                              |
| Design Wavelength DWL (nm):                           | 785                               |
| Damage Threshold, By Design: <input type="checkbox"/> | 5 J/cm <sup>2</sup> @ 785nm, 10ns |


|                             |           |
|-----------------------------|-----------|
| Regulatory Compliance       |           |
| RoHS 2015:                  | Compliant |
| Certificate of Conformance: | View      |
| Reach 235:                  | Compliant |

## Product Details

- <0.25% Reflection at 785nm
  - BBAR Coating Options Also Available: [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
  - [405nm](#), [532nm](#), [633nm](#), 785nm, [980nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered
- TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are designed for maximum throughput at the specified laser wavelength. These lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components. TECHSPEC® 785nm Laser Line Coated Plano-Convex (PCX) Lenses are available Laser V-Coated in a range of other wavelengths: [405nm](#), [532nm](#), [633nm](#), [980nm](#), [1064nm](#), and [1550nm](#). Other coating options are available, including [uncoated](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#).



## Technical Information



## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

