


[See all 3 Products in Family](#)

TECHSPEC® 920nm Laser Line Mirror, 45° AOI, 25.4mm Dia., 6.35mm Thick



920nm Laser Line Mirrors

Stock **#27-558** **20+ In Stock**

⊖ 1 ⊕ **S\$240⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1-5	S\$240.80 each
Qty 6-25	S\$191.80 each
Qty 26-49	S\$180.60 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

25.40 +0.00/-0.10 **Diameter (mm):**

Commercial Polish **Back Surface:**

90 **Clear Aperture (%):**

<3 **Parallelism (arcmin):**

6.35 ± 0.20 **Thickness (mm):**

Optical Properties

905 - 935 **Wavelength Range (nm):**

Fused Silica (Corning 7980) **Substrate:**

Laser Mirror (905-935nm) **Coating:**

Coating Specification:
R_{abs} 99.80% @ 920nm @ 45° AOI
R_{avg} 99.5% @ 905 - 935nm @ 45° AOI

λ/10 **Surface Flatness (P-V):**

10-5 **Surface Quality:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- >99.8% Absolute Reflectivity at 920nm
- 99.5% Average Reflectivity in the 905 - 935nm Range
- High Laser Damage Threshold
- Wide Range of Laser Line Mirrors Options Available

TECHSPEC® 920nm Laser Line Mirrors are designed with an absolute reflectivity of >99.8% at 920nm at a 45° angle of incidence. These mirrors are manufactured from high quality fused silica and are designed for use with high power laser sources. Available in standard 12.7, 25.4, and 50.8mm sizes, these mirrors can be easily integrated into existing laser systems. TECHSPEC® 920nm Laser Line Mirrors feature λ/10 surface flatness and 10-5 surface quality to ensure reduced scattering in sensitive laser applications. These mirrors are ideal for applications including two-photon (2P) microscopy, medical imaging, and material processing.