

[See all 70 Products in Family](#)

TECHSPEC<sup>®</sup> 9mm Diameter, 1550nm V-Coat,  $\lambda$ /4 N-BK7 Window

See More by [SCHOTT Optical Components](#)



Stock #83-526 11 In Stock

-

1

+

S\$139<sup>30</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | S\$139.30 each                |
| Qty 6-25       | S\$112.00 each                |
| Qty 26-49      | S\$104.30 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Laser Line Window                | Type:                   |
| Physical & Mechanical Properties |                         |
| 8.10                             | Clear Aperture CA (mm): |
| 9.00 +0.00/-0.25                 | Diameter (mm):          |

|                      |                                       |
|----------------------|---------------------------------------|
| 2.00 ±0.20           | Thickness (mm):                       |
| ≤1                   | Parallelism (arcmin):                 |
| Protective as needed | Bevel:                                |
| 90                   | Clear Aperture (%):                   |
| Fine Ground          | Edges:                                |
| 0.21                 | Poisson's Ratio:                      |
| 82                   | Young's Modulus (GPa):                |
| 610.00               | Knoop Hardness (kg/mm <sup>2</sup> ): |

|                                  |                                        |
|----------------------------------|----------------------------------------|
| Optical Properties               |                                        |
| Laser V-Coat (1550nm)            | Coating:                               |
| 1550                             | Design Wavelength DWL (nm):            |
| N-BK7                            | Substrate: <input type="checkbox"/>    |
| 1.516                            | Index of Refraction (n <sub>d</sub> ): |
| 60-40                            | Surface Quality:                       |
| 64.17                            | Abbe Number (v <sub>d</sub> ):         |
| R <sub>abs</sub> <0.25% @ 1550nm | Coating Specification:                 |
| λ/4                              | Surface Flatness (P-V):                |

|                                           |                                                              |
|-------------------------------------------|--------------------------------------------------------------|
| Material Properties                       |                                                              |
| 2.51                                      | Density (g/cm <sup>3</sup> ):                                |
| 7.1 (-30 to +70°C)<br>8.3 (+20 to +300°C) | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |

|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

- <0.25% Reflection at Design Wavelength
- Coatings Available for HeNe, Diode, and Nd:YAG Laser Sources
- Precision N-BK7 Substrate
- Also Available [Uncoated](#), [MgF<sub>2</sub> Coated](#) and [VIS 0° Coated](#)

TECHSPEC® λ/4 N-BK7 Laser Line Windows are ideally suited for industrial and low power laser applications. The high tolerance design yields minimal beam distortion and scatter. Anti-reflection coatings provide <0.25% reflection at the coating's design wavelengths.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

## Technical Information



# Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts

;