

[See all 43 Products in Family](#)

Model 1137, 7mW Random Polarization, Lumentum HeNe Laser



Lumentum High Performance Helium-Neon Lasers



Stock #62-724 CLEARANCE CONTACT US

⊖ 1 ⊕ **SS\$1,911⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	SS\$1,911.00 each
Need More?	Request Quote

Product Downloads



General

10	Warm-Up Time (minutes):
Lumentum	Manufacturer:
HeNe	Type of Laser:
IIIb	Laser Class - CDRH:

1137 **Model Number:**

Physical & Mechanical Properties

Pointing Stability after Warm Up (mrad/°C):
After 15 min: <0.02

Weight (lbs):
1.3

Length of Laser Head (inches):
15.79

Static Alignment:
Centered to Outer Cylinder: $\pm 0.01''$
Parallel to Outer Cylinder: ± 1.0 mrad

Pointing Stability (mrad/°C):
From Cold Start, 25°: <0.1

Diameter of Laser Head (inches):
1.74

Optical Properties

Polarization:
Random

Spatial Mode:
TEM₀₀

Wavelength (nm):
632.80

Beam Diameter Tolerance (%):
 ± 3

Beam Divergence Tolerance (%):
 ± 3

Maximum Drift:
Mean Power over 8 hrs: ± 2.5

Beam Diameter (mm):
0.81

Beam Divergence (mrad):
1.00

Color:
Red

Mode Purity (TEM₀₀):
>95%

Electrical

Output Power (mW):
7

RMS Noise:
30 Hz - 10 MHz 0.2%

Longitudinal Mode Spacing, Nominal (MHz):
435

Minimum Output Power, TEM₀₀ (mW):
7.0

Hardware & Interface Connectivity

Power Supply:
[#18-965](#) or [#18-969](#) (12VDC), [#18-966](#) (24VDC),
[#11-390](#) (110/220VAC)

Output Type:
Free Space

Environmental & Durability Factors

Operating Temperature (°C):
-40 to +70

Operating Humidity:
0 to 100%, non-condensing

Storage Temperature (°C):
-40 to +150

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

Product Details

110V or 220V power supplies sold separately. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993.

- Power Options from 0.5 - 22.5mW
- Improved Stability
- Ideal for Interferometry and Metrology Applications
- Random or Linear Polarization Options

Lumentum High Performance Helium-Neon Lasers feature a patented close-cathode design that provides improved thermal and power stability. They also utilize a patented field concentrator design that enables fast turn-on. These Lumentum HeNe lasers also feature precisely aligned cylindrical housings, with cylindrical laser heads and electrical interconnect systems used to simplify system integration. Lumentum High Performance Helium-Neon Lasers' rugged design is ideal for even the most demanding applications. They are exemplary for use within interferometry and metrology applications.

Note: Please exercise caution when using a user-provided power supply to not exceed the electrical specifications of the laser as this may cause damage and void the warranty. These HeNe lasers comply with 21CFR1040 and IEC 825-1:1993. Lumentum was previously known as JDSU.

Technical Information

Beam Expander Mounting Configurations

Click on an item below to be brought to that item's product page.

