

[See all 146 Products in Family](#)

Allied Vision Alvium 1800 U-050m, 1/3.6" 0.5MP S-Mount, USB 3.0 Monochrome Camera

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Full Housing, S-Mount (Front)



Stock **#14-857** **1 In Stock**

[Similar Cameras](#)

⊖ 1 ⊕ **S\$378⁰⁰**

ADD TO CART

Volume Pricing

Qty 1+	S\$378.00 each
Need More?	Request Quote

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

1800 U-050m **Model Number:**

Allied Vision
Alvium

Manufacturer:
Camera Series:

Physical & Mechanical Properties

33 x 29 x 29 (includes connectors and lens mount)

Dimensions (mm):
Weight (g):

60

Housing:

Full

Sensor

256KB

Image Buffer:

1/3.6"

Sensor Format:

0.50

Resolution (Megapixels):

115.00

Frame Rate (fps):

808 x 608

Pixels (H x V):

4.8 x 4.8

Pixel Size, H x V (µm):

3.9 x 2.9

Sensing Area, H x V (mm):

ON Semi PYTHON 480

Imaging Sensor:

Progressive Scan CMOS

Type of Sensor:

Global

Shutter Type:

8/10 bit

Pixel Depth:

64µs - 10s

Exposure Time:

54

Dynamic Range (dB):

USB3 Vision v1.0, GenICam

Machine Vision Standard:

Electrical

1.5

Power Consumption (W):

Hardware & Interface Connectivity

USB 3.0 Gen 1

Interface:

USB 3.0 Gen 1, Micro-B

Connector:

Power over USB or via GPIO

Power Supply:

4 Programmable TTL GPIOs

GPIOs:

Hardware Trigger (GPIO) or Software Trigger

Synchronization:

Back Panel

Interface Port Orientation:

7-pin JST

GPIO Connector Type:

Threading & Mounting

S-Mount (M12 x 0.5)

Mount:

¼-20 and M6 with Tripod Mount Adapter [#14-156](#)

Mounting Threads:

Environmental & Durability Factors

-20 to +65 (housing temperature)

Operating Temperature (°C):

-20 to +85

Storage Temperature (°C):

Regulatory Compliance

[Compliant](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Compliant](#)

Reach 240:

Product Details

- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALMUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- Up to 24.60 MegaPixels, 1.2" Sensor Format
- [Allied Vision Avium Right Angle USB 3.1 Cameras](#) Also Available

Allied Vision Avium USB 3.0 Cameras feature a lightweight compact form factor with ALMUM® System on Chip (SoC) technology, offering a comprehensive image processing library for advanced onboard image correction and preprocessing functions to relieve host computer and processor workload. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Avium USB 3.0 Cameras feature a USB port on the back panel and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.

;