

[See all 127 Products in Family](#)

Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP CS-Mount, Right Angle USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Allied VSION Alvium Camera, Full Housing, CS-Mount, Right Angle IO Port (Front)

Stock **#14-136** [CONTACT US](#)

[Similar Cameras](#)

- 1 + **S\$420^{.00}**

ADD TO CART

Volume Pricing	
Qty 1+	S\$420.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads	
Monochrome	Spectrum:
General	
Monochrome Camera	Type:
Model Number:	

1800 U-500m	
Allied Vision	Manufacturer:
Alvium Right Angle	Camera Series:
Physical & Mechanical Properties	
33 x 32 x 29 (includes connectors and lens mount)	Dimensions (mm):
60	Weight (g):
Full	Housing:
Sensor	
256KB	Image Buffer:
1/2.5"	Sensor Format:
5.00	Resolution (Megapixels):
67.00	Frame Rate (fps):
2,592 x 1,944	Pixels (H x V):
2.2 x 2.2	Pixel Size, H x V (µm):
5.7 x 4.3	Sensing Area, H x V (mm):
ON Semi AR0521	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Rolling	Shutter Type:
8/10 bit	Pixel Depth:
13µs - 849ms	Exposure Time:
63	Dynamic Range (dB):
USB3 Vision v1.0, GenICam	Machine Vision Standard:
Electrical	
2.2	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.1 Gen 1	Interface:
USB 3.1 Gen 1, Micro-B	Connector:
Power over USB or via GPIO	Power Supply:
4 Programmable TTL GPIOs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel (Right Angle)	Interface Port Orientation:
7-pin JST	GPIO Connector Type:
Threading & Mounting	
CS-Mount	Mount:
1/4-20 and M6 with Tripod Mount Adapter #14-156	Mounting Threads:
Environmental & Durability Factors	
+5 to +65	Operating Temperature (°C):
-10 to +70	Storage Temperature (°C):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Right Angle USB Port Orientation
- Compact, Low Cost, High Performance Design for Machine Vision and Embedded Applications
- ALVIUM® System on Chip (SoC) Technology with Onboard Imaging Preprocessing
- [Allied Vision Alvium USB 3.1 Cameras](#) Also Available

Allied Vision Alvium Right Angle USB 3.1 Cameras feature ALVIUM® System on Chip (SoC) technology and a right-angle USB port in a lightweight compact form factor, offering a comprehensive image processing library for advanced onboard image correction, preprocessing functions to relieve host computer and processor workload, and allow for easy system integration. In addition to smart camera operations, the unique SoC design also allows for low power consumption and ease of integration, making them ideal for next generation machine vision, robotics and embedded vision applications. The cameras feature a variety of popular Sony Pregius and On Semi CMOS sensors with high image quality, fast frame rate and USB3 Vision interface standard. The actively aligned lens mount minimizes inconsistency and variation. Allied Vision Alvium Right Angle USB 3.1 Cameras feature a 90° right angle USB port and are available in a variety of monochrome, color, and NIR configurations, including C-Mount, CS-Mount, and S-Mount. Full housing versions are best suited for prototyping, development and end user uses. Partial housing and board level configurations have exposed image sensor PCB without heat sinks to reduce space and facilitate system integration making them ideal for OEM embedded design.

Note: Board level versions do not have a lens mount.