

Clear Optical Path USAF Target 38mm Dia.



Stock **#58-402** **4 In Stock**

-

1

+

S\$1,575^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	S\$1,575.00 each
Qty 5+	S\$1,497.02 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
34.00	Inner Diameter (mm):
38.1	Outer Diameter (mm):
0.01	Thickness (mm):
Anodized Aluminum Mount	Construction:

Housing Tolerance (mm):

±0.01

Optical Properties

Minimum: Group 0, Element 1
Maximum: Group 3, Element 6

Resolution:

Threading & Mounting

Mount Thickness (mm):
1.03

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View


Reach 240:
Compliant

Product Details

- Determine Resolution for X-Ray, UV, Thermal, and Far-IR Imaging Systems
- Easy Mounting
- Ideal for Transmittance Applications

Our Clear Optical Path USAF targets are manufactured from an extremely thin electroformed nickel substrate. Since there is no glass in the pattern area, light travels only through air, eliminating chromatic and absorption issues. The target pattern covers from Group 0, Element 1 to Group 3, Element 6. A user card is included to illustrate where each group and element is located. Our [UV Fused Silica & fluorescent USAF targets](#) are available for most NUV applications, but the Clear Optical Path Target can be used for very deep UV and far-IR applications. The electroform pattern is mounted between two circular plates, allowing it to be mounted in our standard optic mount, [#64-565](#).

Technical Information



Element	Group No.			
	0	1	2	3
1	1.00	2.00	4.00	8.00
2	1.12	2.24	4.49	8.98
3	1.26	2.52	5.04	10.10
4	1.41	2.83	5.66	11.30
5	1.59	3.17	6.35	12.70
6	1.78	3.56	7.13	14.30