

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110573 | 1000μJ-2000mJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock #12-388 [CONTACT US](#)

⊖ 1 ⊕ S\$2,730⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,730.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:
J-50MB-HE
Coherent Part Number: 1110573

Type:
[Meter required](#)

Linearity (%):
±3

Calibration Uncertainty (%):
±2

<33 **Noise Equivalent Energy (μ J):**

[#88-412](#) or [#35-203](#) **Compatible Meters:**

Maximum Incident Energy Density:
500mJ/cm² (10ns, 1064nm)

1mJ - 2J **Energy Range:**

[#66-277](#) **Preferred Meter:**

Physical & Mechanical Properties

50 **Active Area Diameter (mm):**

Optical Properties

1064 **Calibration Wavelength (nm):**

57 **Maximum Pulse Width (μ s):**

190 - 12000 **Wavelength Range (nm):**

Sensor

Pyroelectric **Type of Sensor:**

Electrical

300 **Maximum Repetition Rate (pps):**

10 **Maximum Incident Beam Power (W):**

Hardware & Interface Connectivity

DB25 **Connector:**

2.5 **Length of Cable (m):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[Contains SVHC\(s\)](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.