

[See all 15 Products in Family](#)

Coherent® EnergyMax 1110856 | 100nJ-200μJ, DB25

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#12-385** [CONTACT US](#)

-

1

+

S\$2,555^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,555.00 each
Need More?	Request Quote

Product Downloads

General	
J-10MT-10KHZ Coherent Part Number: 1110856	
Model Number:	
Type:	
Meter required	
Linearity (%):	
±3	
Calibration Uncertainty (%):	
±2	

<10	Noise Equivalent Energy (μJ):
	Compatible Meters:
#35-203	

Maximum Incident Energy Density: 50mJ/cm² (10ns, 1064nm)	
100nJ - 200μJ	Energy Range:
	Preferred Meter:
#88-412	

Physical & Mechanical Properties

Active Area Diameter (mm):	
10	

Optical Properties

Calibration Wavelength (nm):	
1064	
Maximum Pulse Width (μs):	
1.7	

Wavelength Range (nm):	
190 - 2100	

Sensor

Type of Sensor:	
Pyroelectric	

Electrical

Maximum Repetition Rate (pps):	
10000	
Maximum Incident Beam Power (W):	
1	

Hardware & Interface Connectivity

Connector:	
DB25	
Length of Cable (m):	
2.5	

Regulatory Compliance

RoHS 2015:	
Exempt	
Reach 224:	
Contains SVHC(s)	

Certificate of Conformance:	
View	

Product Details

- ISO 17025 Certified
- Embedded Spectral Compensation Characteristics
- Automatic Temperature Compensation

Coherent® EnergyMax Laser Energy Sensors are designed for a variety of demanding laser measurement applications. These energy sensors, available in meter or meterless USB configurations, incorporate a diffuse coating to minimize specular reflection and feature large active areas. The J-50MB-YAG combines the MaxBlack coating with a diffuser for use with high energy lasers of up to 3J. Coherent® EnergyMax Laser Energy Sensors utilize onboard sensors to automate temperature compensation for improved measurement accuracy.