

Coherent® OBIS™ FP 1253283 | 488nm LS 40mW Laser, Fiber Pigtail, FC

See More by [Coherent®](#)



Coherent® High Performance OBIS™ Fiber-Pigtailed Laser Systems



Stock #12-362 [CONTACT US](#)

⊖ 1 ⊕ **\$\$12,068⁰⁰**

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | \$\$12,068.00 each |
| Need More? | Request Quote |

Product Downloads



General

Warm-Up Time (minutes):
<5

Fiber Cable Type:
5mm Protective Tubing

Manufacturer:
Coherent®

Type of Laser:

| | |
|---|---|
| Diode | |
| IIIb | Laser Class - CDRH: |
| 1253283 | Model Number: |
| Optical Properties | |
| 100:1 | Polarization: |
| TEM ₀₀ | Spatial Mode: |
| 488.00 ±2 | Wavelength (nm): |
| ≤1.1 | Mode Quality, M²: |
| Blue | Color: |
| 0.06 | Fiber Numerical Aperture NA (1/e²): |
| Electrical | |
| 40 | Output Power (mW): |
| <2 | Power Stability (%): |
| Digital: 0.05 | Modulation Frequency (MHz): |
| Analog: 500 | Modulation Frequency (kHz): |
| ≤0.25% (20Hz to 20MHz) | RMS Noise: |
| Hardware & Interface Connectivity | |
| Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473 | |
| FC/APC; 8° angled | Output from Fiber: |
| Fiber-Coupled | Output Type: |
| Environmental & Durability Factors | |
| 10 to 50 | Operating Temperature (°C): |
| Regulatory Compliance | |
| Exempt | RoHS 2015: |
| Contains SVHC(s) | Reach 224: |
| View | Certificate of Conformance: |

Product Details

- High Performance OBIS™ LX/LS Lasers with Added Fiber Optic Capability
- Permanent Fiber Attachment Extends Lifetime with Guaranteed Power
- Single-Mode Polarization-Maintaining Fiber with an FC/APC Connector Provide High-Quality and Low-Noise Laser Beam Output
- [Coherent® High Performance OBIS™ LX/LS Laser Systems](#) Also Available

Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems are plug-and-play lasers available in wavelengths from the ultraviolet to the near-infrared with an added fiber attachment. The fiber optic is permanently attached to the laser, providing an extended lifetime of the fiber and guaranteed power consistency. An FC/APC connector terminates the fiber to enable connections to other systems without concern for high noise interference. Coherent® High Performance OBIS™ LX/LS Fiber-Pigtailed Laser Systems produce high-quality, low-noise laser beams and also allow for hands-free operation. These fiber-pigtailed lasers are used in confocal microscopy, DNA sequencing, polymerase chain reaction (PCR) diagnostic instruments, flow cytometry, medical imaging, and instrumentation applications.

OBIS Laser System Startup Guide

This downloadable PDF provides guidance on interfacing with OBIS controllers and power supplies, mounting and connecting the heatsink, and starting modulation.

[Download Startup Guide](#)

