

[See all 10 Products in Family](#)

Coherent® PowerMax USB PM30 Measurement System 1174257 | 10mW-30W

See More by [Coherent®](#)



Stock **#12-410** [CONTACT US](#)

-

1

+

S\$2,618^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$2,618.00 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	
PM30 Coherent Part Number: 1174257	
Type:	
Meterless	
Calibration Uncertainty (%):	
±2	
Long Pulse Joule Mode Range (J):	

0.5 - 50	
Air	Cooling Method:
	Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns
Physical & Mechanical Properties	
19	Active Area Diameter (mm):
Optical Properties	
10600	Calibration Wavelength (nm):
190 - 11000	Wavelength Range (nm):
0.19 - 11	Wavelength Range (µm):
Sensor	
Thermopile	Type of Sensor:
Electrical	
±1.5	Spectral Compensation Accuracy (%):
50 (air-cooled)	Maximum Intermittent Power, <5min (W):
6	Maximum Incident Power Density (kW/cm²):
10mW - 30W	Power Range:
Hardware & Interface Connectivity	
2.5	Length of Cable (m):
USB	Computer Interface:
Regulatory Compliance	
Exempt	RoHS 2015:
Contains SVHC(s)	Reach 224:
View	Certificate of Conformance:

Product Details

- Superior Damage Resistance
- Wide Dynamic Range
- ISO 17025 Certified

Coherent® Thermopile Power Sensors are ideal for measuring the average power of continuous wave lasers or pulsed laser energy. Thermopile sensors operate by absorbing and converting incident laser radiation into heat, which then flows to a heat sink. The temperature difference between the absorber and heat sink is converted into an electrical signal by a thermocouple junction. Coherent® Thermopile Power Sensors, unlike semiconductor sensors, do not saturate. Unlike semiconductor sensors, thermopile sensors feature high power capability and flat spectral response.