

[See all 11 Products in Family](#)

Blue 405nm, MicroBrite LED Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite Spot Light

Stock **#90-470** NEW **1 In Stock**

-

1

+

S\$497^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	S\$497.00 each
Need More?	Request Quote

Product Downloads

General	
SL223S-405IC	Model Number:
50,000	LED Lifetime (hours):
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:

Geometry:

Spot Light	
Constant	Illumination Mode:
Physical & Mechanical Properties	
7.90	Diameter (mm):
1/4	Fiber Bundle Diameter (inches):
38.10	Length (mm):
0.312	Outer Diameter (inches):
Optical Properties	
Blue	Color:
405	Wavelength (nm):
Hardware & Interface Connectivity	
Flying Leads	Connector:
Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	Power Supply:
2	Length of Cable (m):
Environmental & Durability Factors	
0 - 50	Operating Temperature (°C):
IP65	Environmental Rating:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Port
- IP65 Rated - Protection from Dust and Water Spray
- 50,000 Hour Lifetime

Advanced Illumination MicroBrite Spot Lights are designed to replace fiber optic illumination systems used in microscopes and machine vision applications. They serve as drop in replacements for any 1/4" or 8mm fiber light guide, or can combine with light guide adapters to replace large fiber bundles. Advanced Illumination MicroBrite Spot Lights are 25X brighter than standard spot lights, feature low power consumption, and a 50,000 hour lifetime.

Note: The 24V Power Supply required for operation ([#66-855](#)) is not included. Units cannot be intensity controlled.

3D-Printable Mount Files



Spot Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#) 