

Deuterium-Tungsten Spectroscopy Illuminator

See More by [Ocean Optics](#)



Stock **#90-546** NEW **2 In Stock**

-

1

+

\$7,056⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	\$7,056.00 each
Need More?	Request Quote

Product Downloads

General	
Deuterium-Tungsten Illuminator	Type:
DH-2000-BAL	Model Number:
Power supply and integrated shutter included.	Note:
1000	Operating Lifetime (hours):
Physical & Mechanical Properties	

5.5	Weight (kg):
Optical Properties	
210 - 2500	Wavelength Range (nm):
Electrical	
TTL, Up to 2.5 Hz maximum	Trigger:
Deuterium: 194 Tungsten Halogen: 615	Output Power (µW):
Hardware & Interface Connectivity	
SMA905	Connector:
85–264 V 50/60 Hz	Power Requirement:
Environmental & Durability Factors	
5 to 35	Operating Temperature (°C):
5–95% without condensation at 40°C	Operating Humidity:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Stable, High-Quality Output Across Broad Wavelength Ranges from 185–2500 nm
- Deuterium-Tungsten, Xenon, Tungsten-Halogen Lamp Types Available
- Fully Compatible with Ocean Optics Spectrometers and Accessories

Ocean Optics Spectroscopy Illuminators offer a flexible range of UV–NIR light sources to pair with Ocean Optics spectroscopy systems. Choose from Tungsten-Halogen for stable VIS–NIR output (360–2400nm), Xenon for high-intensity, pulsed broadband UV–NIR illumination (185–2500nm), or Deuterium-Tungsten for continuous coverage from deep UV through NIR (210–2500nm). Typical applications include reflectance, transmittance, absorbance, and fluorescence measurements where reliable, well-matched illumination is essential. Ocean Optics Spectroscopy Illuminators are designed for lifetimes of up to 10,000 hours and feature SMA fiber connections.