

Preloaded Norland Optical Adhesive NOA 68TH Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA 60 shown as an example)

Stock **#14-789** **6 In Stock**

-

1

+

S\$38^{.50}

ADD TO CART

Volume Pricing	
Qty 1-11	S\$38.50 each
Qty 12-19	S\$34.72 each
Need More?	Request Quote

Product Downloads

General	
0.1	Size (oz):
68TH	Norland Number:
4 months	Shelf Life:
Barrel	Type:

Typical Applications:
Screen printable, high viscosity optical adhesive that can be UV cured and/or heat cured.

Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.

Optical Properties	
Refractive Index (n)	1.50
Transmittance (%)	95.0
Absorbance (A)	0.05
Color	Colorless
Fluorescence	None

1.54 @ 589nm

Index of Refraction (n_d):

350 - 380

Absorption Range (nm):

Material Properties	
---------------------	--

Excellent

Glass Bonding:

Good

Metal Bonding:

Excellent/Good

Plastic Bonding:

20,000 - 25,000

Viscosity (cps):

Plastic to Plastic/Glass

Bonding Type:

4.5

Energy for Full Cure (J/cm²):

Environmental & Durability Factors

Flexible

Durability:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 251:

Product Details

- Dispensing Syringes Preloaded with 2 or 10g of Adhesive
- Adhesives for Glass, Metal, and Plastic Bonding
- Require a Dispensing Unit & Dispenser Tips for Use
- **Applicator and Bulk Bottles** of Norland Adhesive Also Available

Preloaded Norland Optical Adhesive Syringes are pneumatic dispensing syringes preloaded with either 2g or 10g of Norland Optical Adhesive. Norland Optical Adhesives are one-part, UV curing adhesives that are used for glass, metal, and plastic bonding. A range of adhesives are available to meet specific application requirements such as ML-A-3920 for defense applications, low outgassing for aerospace applications, or UV transmission for UV optical applications. Preloaded Norland Optical Adhesive Syringes require a [dispensing unit](#) and [dispensing tips](#) for use and are ideal for applications requiring precise control of the amount of applied adhesive. Applicators and Bulk Bottles of Norland Adhesive are also available.

Technical Information

NORLAND OPTICAL ADHESIVES (NOA) APPLICATION NOTES	
Title	Description
Applying Adhesive	Covers best practices to use when applying Norland Optical Adhesives to ensure an even adhesive layer while avoiding air bubbles.
Chemical Resistance of NOA	Covers the effects of various chemicals on Norland Optical Adhesives including acids, bases, and solvents.
Preventing Lens Separations with NOA	Covers best practices to avoid adhesive failures when bonding optical elements.
Separating Lenses Bonded with NOA	Covers how to unbond optical elements bonded with Norland Optical Adhesives.

