

TECHSPEC[®] Complete Achromat Prototyping Kit



Stock **#54-666** [CONTACT US](#)

-

1

+

S\$1,717^{.53}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$1,717.53 each
Qty 6-10	S\$1,512.76 each
Qty 11-25	S\$1,392.38 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Prototyping Kit

Type:

Kit

Function:

Regulatory Compliance	
-----------------------	--

Compliant

View

- Imaging Lens System for Prototyping
- Ideal for Identifying Desired Magnification and $f/\#$
- Compatible with Helicoid Barrel for Use With C-M

A pair of achromats can offer surprising performance in imaging applications. This system enables experimentation with different focal length ratios to achieve a variety of magnifications and fields of view. The camera sensor and object should be placed at the focal length of the image and object achromat, respectively (see diagram). The $f\#$ of the lens can be varied by using different apertures. The aperture is a center spacer that slides (no threads) into place between the achromats. Proper focusing can be attained using [C-Mount spacers](#) (coarse) and the [Helicoid Barrel](#) (fine). The Achromat Prototyping cell threads directly into the helicoid barrel and retainers are used to fix the relative position of the cell. Only [12.5mm diameter achromats](#) can be used with this system. Achromat prototyping kit ([#54-666](#)) includes helicoid barrel, achromat prototyping cell, two retaining rings (15mm, for inside helicoid barrel) and [12.5mm achromat kit](#). Achromat prototyping cell ([#54-719](#)) includes the mounting cell, two retainers (for inside mounting cell) and aperture kit. Aperture kit ([#54-720](#)) contains seven apertures of 0.0 (customizable by user), 2.0, 3.0, 4.0, 6.0, 8.0, and 10.6mm diameters.

Image Achromat Focal Length													
Object FL	14.0	20.0	25.0	30.0	35.0	40.0	45.0	50.0	60.0	75.0	80.0	90.0	100.0
14.0	1.00*	1.43	1.79	2.14	2.50	2.86	3.21	3.57	4.29	5.36	5.71	6.43	7.14
20.0	0.70*	1.00	1.25	1.50	1.75	2.00	2.25	2.50	3.00	3.75	4.00	4.50	5.00
25.0	0.56*	0.80	1.00	1.20	1.40	1.60	1.80	2.00	2.40	3.00	3.20	3.60	4.00
30.0	0.47*	0.67	0.83	1.00	1.17	1.33	1.50	1.67	2.00	2.50	2.67	3.00	3.33
35.0	0.40*	0.57	0.71	0.86	1.00	1.14	1.29	1.43	1.71	2.14	2.29	2.57	2.86
40.0	0.35*	0.50	0.63	0.75	0.88	1.00	1.13	1.25	1.50	1.88	2.00	2.25	2.50
45.0	0.31*	0.44	0.56	0.67	0.78	0.89	1.00	1.11	1.33	1.67	1.78	2.00	2.22
50.0	0.28*	0.40	0.50	0.60	0.70	0.80	0.90	1.00	1.20	1.50	1.60	1.80	2.00
60.0	0.23*	0.33	0.42	0.50	0.58	0.67	0.75	0.83	1.00	1.25	1.33	1.50	1.67
75.0	0.19*	0.27	0.33	0.40	0.47	0.53	0.60	0.67	0.80	1.00	1.07	1.20	1.33
80.0	0.18*	0.25	0.31	0.38	0.44	0.50	0.56	0.63	0.75	0.94	1.00	1.13	1.25
90.0	0.16*	0.22	0.28	0.33	0.39	0.44	0.50	0.56	0.67	0.83	0.89	1.00	1.11
100.0	0.14*	0.20	0.25	0.30	0.35	0.40	0.45	0.50	0.60	0.75	0.80	0.90	1.00
*Image FL of 14 is not recommended for C-Mount Cameras													

Image Achromat Focal Length													
Aperture Diameter	Image Achromat Focal Length												
	14.0	20.0	25.0	30.0	35.0	40.0	45.0	50.0	60.0	75.0	80.0	90.0	100.0
10.60	1.32	1.89	2.36	2.83	3.30	3.77	4.25	4.72	5.66	7.08	7.55	8.49	9.43
8.00	1.75	2.50	3.13	3.75	4.38	5.00	5.63	6.25	7.50	9.38	10.00	11.25	12.50
6.00	2.33	3.33	4.17	5.00	5.83	6.67	7.50	8.33	10.00	12.50	13.33	15.00	16.67
4.00	3.50	5.00	6.25	7.50	8.75	10.00	11.25	12.50	15.00	18.75	20.00	22.50	25.00
3.00	4.67	6.67	8.33	10.00	11.67	13.33	15.00	16.67	20.00	25.00	26.67	30.00	33.33
2.00	7.00	10.00	12.50	15.00	17.50	20.00	22.50	25.00	30.00	37.50	40.00	45.00	50.00
Application Note: Achromat pairs used at moderate f/#s (f/4 - f/8) provide good aberration correction for applications that do not require wide fields of view.													

