

TECHSPEC® Elliptical Mirror 26.97mm Minor Axis Protected Aluminum



Stock #30-837 3-5 DAYS

- 1 + **S\$127.60**

ADD TO CART

Qty 1-5
S\$127.60
Qty 6+
S\$102.22
Volume Pricing
Request Quote

Get Product Downloads



Minor Axis (mm):
26.97

Major Axis (mm):
38.15

Surface Flatness (P-V):
λ/8

Substrate: ☐

BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Clear Aperture CA (mm): 24.28 (Minor Axis) 34.34 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 6.35
Thickness Tolerance (inches): ±0.030
Thickness Tolerance (mm): ±0.76
Type: Flat Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: ☐ 0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant