

TECHSPEC[®] Elliptical Mirror 38.1mm Minor Axis Enhanced Aluminum



Stock #32-134 3-5 DAYS

-

1

+

S\$203.00

ADD TO CART

Qty 1-5

S\$203.00

Qty 6+

S\$162.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Minor Axis (mm):
38.10

Major Axis (mm):
53.87

Surface Flatness (P-V):
λ/8

Substrate:

BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 34.29 (Minor Axis) 48.49 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 9.53
Thickness Tolerance (inches): ±0.030
Thickness Tolerance (mm): ±0.76
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant