

E Series 12mm 2⁄3" Format Fixed Focal Length Lens



E Series 12mm 2⁄3" Format Fixed Focal Length Lens



Stock **#29-996** **5 In Stock**

-

1

+

S\$362⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$362.60 each
Need More?	Request Quote

Product Downloads

General	
E Series	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:

33.76	Length (mm):
26.5	Maximum Diameter (mm):
26.5	Outer Diameter (mm):
2.98	Maximum Rear Protrusion (mm):

Optical Properties	
50.17°	Horizontal Field of View @ Max Sensor Format:
50.17°	Horizontal Field of View, 2/3" Sensor:
41.91°	Horizontal Field of View, 1/1.8" Sensor:
37.60°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
7 (6)	Number of Elements (Groups):
400 - 700	Wavelength Range (nm):
12.00	Focal Length FL (mm):
250 - ∞	Working Distance (mm):
f/4 - f/16	Aperture (f/#):
M4 MgF ₂	Coating:
13.02	Entrance Pupil Position (mm):
20.21	Object Space Principal Plane (mm):
-1.61	Image Space Principal Plane (mm):
0.96	Maximum Distortion (%):
-19.19	Exit Pupil Position (mm):
VIS	Lens Wavelength Range:

Sensor	
2/3"	Maximum Sensor Format:
2.74	Pixel Size (µm):

Threading & Mounting	
M25.5 x0.5 (Female)	Filter Thread:
M25.5 x0.5 (Female)	Front Thread:
C-Mount	Mount:

Environmental & Durability Factors	
-20 to +60 For questions regarding operating temperature please contact our support team	

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Cost Effective Solution for Systems that Require Large Depth of Field
 - Up to ⅜", C-Mount Lens
 - Ideal for Logistics and Barcode Scanning Applications
- Edmund Optics E Series Fixed Focal Length Lenses provide an affordable fixed focal length imaging solution without compromising performance. These lenses are designed for logistics applications that need to identify product size

and shape, read barcodes, and help find product locations. These systems often don't require lenses designed with more demanding specifications like large format sensor coverage and small pixels, which can be costly. Edmund Optics E Series Fixed Focal Length Lenses are a balance of performance and cost designed with a maximum format of 2/3". To maintain affordability in prototyping and mass production, the lens housings have been simplified by removing focusing mechanics. However, the focus can still be adjusted by threading the lenses into and out of the camera, then locked with a locking ring. These lenses maintain performance control with an adjustable iris ranging from f/4 to f/16.

;