

[See all 20 Products in Family](#)

Efflux Blue EFFI-Lase Structured LED Lighting Projector with Matrix Pattern (Recertified 05-P)



Efflux EFFI-Lase Structured LED Lighting Projector

Stock **#22-124-RCD-05P** RECERTIFIED **2 In Stock**

-

1

+

S\$1,398⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	S\$1,398.60 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General	
EFFI-LASE-PSV-MX1-465-ZZZ	Model Number:
LED Illuminator	Type of Illumination:

Efflux	Manufacturer:
--------	---------------

3D Projector	Geometry:
Strobe or Constant	Illumination Mode:
Physical & Mechanical Properties	
79.1 x 129.6	Dimensions (mm):
Optical Properties	
Blue	Color:
465	Wavelength (nm):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #73-409 Korea: #73-409 China: #15-874	
Environmental & Durability Factors	
0 to 40	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High Accuracy Without Speckle
- Wide Range of Standard Masks Available
- White, Blue, Red, and IR Colors Available
- Compatible with [C Series Fixed Focal Length Lenses](#) and [HP Series Fixed Focal Length Lenses](#) for Pattern Projection

Effilux EFFI-Lase Structured LED Lighting Projectors produce accurate, intense, and uniform lines, matrices, crosses, and arrays of points. Featuring an integrated driver board and easily interchangeable masks, these projectors are ready for plug and play use. Passive cooling and a temperature protection system ensure stable operation and help to prevent damage for long term operation. Effilux EFFI-Lase Structured LED Lighting Projectors offer the accuracy, power, and homogeneity of a laser projector without the speckle. These projectors are ideal for a range of machine vision applications such as 3D reconstruction, stereovision, and alignment.

Note: Masks sold separately, see accessories tab for options. Designed for use with a C-mount lens for pattern projection. 1.1" sensor lenses are recommended for masks with rectangular patterns to reduce distortion while 2/3" sensor lenses are sufficient for all other applications.