

## Gas Flow Cell FCM10, 1/8" Fit, SMA



#72-192

Stock **#72-193** 1 In Stock

⊖ 1 ⊕ **\$\$1,855<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-4	<b>\$\$1,855.00</b> each
Qty 5-9	<b>\$\$1,669.50</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Path Length (cm):  
10

Throughput (%):  
>50%

Fiber Connector Type:  
SMA905

### General

Type:  
FCM

Model Number:  
FCM10-SS-1/8

### Optical Properties

Wavelength Range (nm):  
150 - 9000

## Environmental & Durability Factors

-40 to +200      **Operating Temperature (°C):**

-40 to +200      **Storage Temperature (°C):**

---

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

---

## Product Details

- Free Space and Fiber-Coupled Designs for UV through IR
- Stainless Steel Designs for Operation at High Temperatures and Pressures
- Designed for Easy Integration

Wavelength References Gas Flow Cells are designed for through-flow laser-based gas interrogation. The cells are housed in a rugged vacuum tight enclosure made of 316 stainless steel and feature Swagelok® tube fittings for gas inflow and outflow. We currently offer the following options:

- FCW (Windowed Gas Flow Cells) are optimized for free space applications with a CaF<sub>2</sub> window on the endcap, and feature a 10 cm path length and >50% transmission from 150nm to 9µm.
  - FCS (Single-Mode Fiber-Coupled Gas Flow Cells) are offered in both single mode and multimode configurations that correspond to 16.7 cm and 76.1 cm path lengths, respectively. Available with FC/PC, FC/APC, SC/PC, or SC/APC connectors, these flow cells feature SMF28e fiber for use in the 1260nm to 1800nm wavelength range, and can be operated from full vacuum to 1000 Torr.
  - FCM (Multimode Gas Flow Cells) are optimized for fiber optic and FTIR spectroscopy, and feature an SMA905 connectorized fiber, a 10 cm path length, and >50% transmission from 150nm to 9µm.
- Wavelength References Gas Flow Cells are ideal for gas sensing, chemical detection, and analytical spectroscopy applications.
-