

TECHSPEC[®]

PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 12.7mm Dia., 6.35mm Thick



Stock #29-520 11 In Stock

-

1

+

S\$434^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	S\$434.00 each
Qty 6-25	S\$411.60 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties

12.70 +0.00/-0.10

Diameter (mm):

6.35 ±0.10

Thickness (mm):

Commercial Polish

Edges:

Bevel:

Protective as needed

Optical Properties

10-5

Surface Quality:

Coating Specification:

R_s > 99.50% @ 840 - 1010nm @ 45° AOI
R_p > 99.50% @ 870 - 980nm @ 45° AOI

0±50 fs² @ 840 - 1010nm @ 45° AOI (s-pol)
0±50 fs² @ 880 - 960nm @ 45° AOI (p-pol)

GDD Specification:

λ/10

Surface Flatness (P-V):

840 - 1010, 870 - 980

Design Wavelength DWL (nm):

0.5J/cm² @ 920nm, 100-on-1, S-Polarization, 5Hz,
Pulse Duration 25fs, 350μm Dia.

Damage Threshold, Reference: □

Regulatory Compliance

View

Certificate of Conformance:

Product Details

- High Femtosecond Laser Damage Threshold exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near 0fs² GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding 0.75J/cm² for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

Coating Curves