

**TECHSPEC®**

**Max PeakPower Low-GDD Ultrafast Dielectric Mirror, 920nm, 45° AOI, 50.8mm Dia., 9.53mm Thick**



Stock #29-525 **10 In Stock**

⊖ 1 ⊕ **\$1,183.00**

**ADD TO CART**

Volume Pricing

Qty 1-5	<b>\$1,183.00</b> each
Qty 6-25	<b>\$1,127.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**Physical & Mechanical Properties**

50.80 +0.00/-0.10 **Diameter (mm):**

9.53 ±0.10 **Thickness (mm):**

Commercial Polish **Edges:**

**Bevel:**

Protective as needed

## Optical Properties

10-5 **Surface Quality:**

**Coating Specification:**  
 $R_s > 99.50\%$  @ 830 - 1010nm @45° AOI  
 $R_p > 99.50\%$  @ 840 - 997nm @45° AOI

**GDD Specification:**  
 $0 \pm 50 \text{ fs}^2$  @ 830 - 1010nm @45° AOI (s-pol)  
 $0 \pm 50 \text{ fs}^2$  @ 861 - 966nm @45° AOI (p-pol)

**Surface Flatness (P-V):**  
λ/10

**Design Wavelength DWL (nm):**  
830 - 1010

**Damage Threshold, Reference:** □  
 $0.75 \text{ J/cm}^2$  @ 920nm, 100-on-1, S-Polarization, 5Hz,  
Pulse Duration 25fs, 350μm Dia.

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- High Femtosecond Laser Damage Threshold exceeding  $0.75 \text{ J/cm}^2$  for 25fs Pulse Duration at 920nm
- > 99.5% Reflectivity with Near Zero Group Delay Dispersion
- [Platinum-Level 2024 Laser Focus World \(LFW\) Innovators Award](#)

TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors utilize an innovative design approach to maximize laser damage threshold for ultrafast pulses. These mirrors boast a near  $0 \text{ fs}^2$  GDD over a broad spectral bandwidth, making them suitable for the most demanding ultrafast applications. A 45° angle of incidence makes them perfectly suitable as turn mirrors in advanced ultrafast laser systems. TECHSPEC® PeakPower High LDT Low GDD Ultrafast Mirrors' high reflectivity ensures minimal loss while maintaining ultrashort pulse durations. The outstanding high laser damage threshold (LDT) values exceeding  $0.75 \text{ J/cm}^2$  for 25fs Pulse Duration at 920nm for these mirrors ensures they will perform even under exceptionally high ultrafast pulse energies.

## Coating Curves